



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	27.0	—
E	—	27.0	—
v	—	—	0.20
w	—	—	—
A	—	—	2.5
A₁	0.5	0.6	0.7
e	—	1.27	—
b	0.60	0.75	0.90
x	—	—	0.30
y	—	—	0.20
y₁	—	—	0.35
S_D	—	0.635	—
S_E	—	0.635	—
Z_D	—	—	—
Z_E	—	—	—