



Unit : mm



Taping code	Package name	Renesas code	Previous code	Dimensions (mm)					Maximum storage No. Transistor/Reel
				A	B	C	D	E	
TAPING-DA1000, TO-92-ELCN-A	TO-92(1)	PRSS0003DB-A	TO-92(1)	19.0	25.0 max	47	200	330	2500
	TO-92(1)	PRSS0003DA-A	TO-92(1), TO-92(1)V	19.0	25.0 max	47	200	330	2500
	TO-92(2)	PRSS0003DB-C	TO-92(2)	19.0	25.0 max	47	200	330	2500
	TO-92(2)	PRSS0003DA-C	TO-92(2), TO-92(2)V	19.0	25.0 max	47	200	330	2500
	TO-92(3)	PRSS0003DE-A	TO-92(3), TO-92(3)V	19.0	25.0 max	47	200	330	2500
	TO-92Mod	PRSS0003DC-A	TO-92Mod, TO-92ModV	19.0	28.0 max	47	200	330	2500
G433019	TO-92*	PRSS0003EA-A	-	17.5	22.5	50	180	352	2000

• Cautions for Storage and Handling