

外形図 Outline drawing


Renesasコード PRBG0324GB-A

RDK-G-001281



1/1

ルネサスエレクトロニクス株式会社
Renesas Electronics Corporation

| | | |
|----------------------|--------------|---------------|
| JEITA Package code | RENESAS code | MASS(TYP.)[g] |
| P-FBGA324-19x19-0.80 | PRBG0324GB-A | 1.10 |



Unit :mm



| Reference Symbol | Dimension in Millimeters | | |
|------------------|--------------------------|-------|-------|
| | Min. | Nom. | Max. |
| D | 18.90 | 19.00 | 19.10 |
| E | 18.90 | 19.00 | 19.10 |
| A | — | — | 2.00 |
| A ₁ | 0.30 | 0.35 | 0.40 |
| Ⓜ | — | 0.80 | — |
| b | 0.49 | 0.54 | 0.59 |
| x ₁ | — | — | 0.15 |
| x ₂ | — | — | 0.08 |
| y | — | — | 0.10 |
| y ₁ | — | — | 0.20 |
| n | — | 324 | — |
| Z _D | — | 1.10 | — |
| Z _E | — | 1.10 | — |

