

US082-INTERPEVZ

The US082-INTERPEVZ Board provides a standard Pmod™ Type 6A (Extended I²C) connector to compatible Renesas MCU kits. The board plugs into the existing Type 2A or 3A Pmod on the MCU board and interposes key pins to create a Type 6A connector.

The US082-INTERPEVZ features Pmod connectors on both sides of the board allowing additional Type 6/6A boards to be connected in a daisy-chained solution with multiple sensors on the same MCU Pmod connector. Because of the standard connector, the US082-INTERPEVZ is the best choice to rapidly create an IoT system with the Renesas Quick-Connect IoT.

Features

- Corrects the pinout of a Pmod on compatible Renesas MCU evaluation kits providing a standardized Type 6A Pmod connector for an I²C Extended interface.

Board Contents

- US082-INTERPEVZ Board




Figure 1. US082-INTERPEVZ Pmod Board

Contents

1. Setup	3
1.1 Required or Recommended User Equipment	3
1.2 Kit Hardware Connections	3
2. Board Design	4
2.1 Schematic Diagram	4
2.2 Bill of Materials	5
2.3 Board Layout	5
3. Ordering Information	6
4. Revision History	6

1. Setup

1.1 Required or Recommended User Equipment

The US082-INTERPEVZ board is used with the evaluation kits listed in [Table 1](#).

Note: This table is not a comprehensive list of supported MCU Kits. See your evaluation kit hardware manual to confirm the Pmod pinout.

Table 1. Renesas MCU Evaluation Kits^[1] that support a Type 6A Pmod when used with the US082-INTERPEVZ

RA	RX	Synergy
EK-RA4W1	RX111-Starter-Kit	PK-S5D9
EK-RA2A1	RX231-Starter-Kit	DK-S3A7
EK-RA4M1	RX23W-Starter-Kit	DK-S128
EK-RA6M1	RX23T-Starter-Kit	TB-S1JA
EK-RA6M2	RX24T-Starter-Kit	TB-S3A6
EK-RA6M3	RX24U-Starter-Kit	DK-S7G2
EK-RA6M3G		

1. This table is not a comprehensive list of supported MCU Kits. See the evaluation kit hardware manual to confirm Pmod pinout.

1.2 Kit Hardware Connections

Follow these procedures to set up the kit as shown on [Figure 2](#).

1. Ensure the MCU evaluation kit being used has a Pmod connector that can be used with the US082-INTERPEVZ (to confirm, see the kit hardware manual). See [Table 2](#) for the pin rerouting map.
2. Plug in the US082-INTERPEVZ to the MCU board connector, being careful to align Pin 1 on the interposer board and MCU kit.
3. Plug in any desired Type 6A Pmod into the other side of the US082-INTERPEVZ.
4. The system is now ready for use.




Figure 2. US082-INTERPEVZ Placed Between TB-S3A3 and US082-ZMOD4450EVZ

2. Board Design




Figure 3. US082-INTERPEVZ Pmod Board (Top)




Figure 4. US082-INTERPEVZ Pmod Board (Bottom)

Table 2. Pmod Pin Mapping on US082-INTERPEVZ

Pin	MCU Side	Type 6A Side
1	GPIO 4	IRQ# (INT)
2	GPIO 5 (SDA)	GPIO 7
3	GPIO 6 (SCL)	GPIO 6 (SCL)
4	GPIO 7	GPIO 5 (SDA)
5	GND	GND
6	VCC	VCC
7	IRQ# (INT)	GPIO 4
8	GPIO 1	GPIO 1
9	GPIO 2	GPIO 2
10	GPIO 3	GPIO 3
11	GND	GND
12	VCC	VCC

2.1 Schematic Diagram




Figure 5. US082-INTERPEVZ Application Schematic

2.2 Bill of Materials

Qty	Reference	Description	PCB Footprint	Part Number
1	J1	CONN SOCKET 12POS 2ROW Vertical SMT	PMOD_VRT_HDR	NPPC062KFMS-RC
1	J2	CONN HEADER 12POS 2ROW Vertical SMT	PMOD_VERT_SOCKET	TSM-106-01-L-DV-P

2.3 Board Layout




Figure 6. Silkscreen Top




Figure 7. Copper Top




Figure 8. Copper Bottom




Figure 9. Silkscreen Bottom

3. Ordering Information

Part Number	Description
US082-INTERPEVZ	Pmod interposer board to convert Type 2A and 3A to Type 6A on older Renesas MCU kits.

4. Revision History

Revision	Date	Description
1.0	Jun 15, 2021	Initial release

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Rev.1.0 Mar 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.