


CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PT557BM	PRSP0020DE-A	FP-20DT / FP-20DTV
	PRSP0020DF-A	—
	PRSP0036JA-A	FP-36DT / FP-36DTV
	PRSP0036JC-A	—



The pin1 is located in the hatching portion

Position dimension of cells (mm)	Z_w	17.9
	Z_L	28.55
	e_w	25
	e_L	19.9
	S_w	55
Thickness (mm)	H_1	7.6
	H_2	2.45
Number of cells	N_w	5
	N_L	14
Maximum storage No. IC/Tray		70
Maximum storage No. IC/Inner box		700
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack