
UNIT: mm



Length: 501 ± 2.0 Thickness: $0.7^{+0.3}_{-0.2}$ Tolerance: ±0.4

Material: Plastic (With Antistatic Finish)

Applied Package	Quantity(pcs)
24-Pin Plastic DIP	MAX. 14
28-Pin Plastic DIP	MAX. 12
42-Pin Plastic DIP	MAX. 8
42-Pin Plastic Shrink DIP	MAX. 12
48-Pin Plastic Shrink DIP	MAX. 10
42-Pin Ceramic Shrink DIP (brazed lead)	MAX. 10
48-Pin Ceramic Shrink DIP (brazed lead)	MAX. 10