


IOH vs VOH (P2_0-P2_7 Drive Capacity=High)

Prepared on Feb. 14, 2008

R8C/2K Group
Vcc=3V

— 85degreesC — 25degreesC
— -40degreesC



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.