





644-PIN TAPE BGA (40x40)



detail of A part



detail of B part



ITEM	MILLIMETERS
D	40.00
E	40.00
ZD	1.585
ZE	1.585
e	1.27
A	1.40±0.30
A1	0.60±0.10
A4	0.25 MIN.
b	0.75±0.15
x	0.15
y	0.20
y1	0.35
V	0.20
W	0.30

S644N7-127-H6