


# CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
M095-36	PRQP0064GA-A	64P6N-A
	PRQP0080JA-A	80P6S-A

Unit:mm



The pin1 is located in the hatching portion

Position dimension of cells (mm)	$Z_w$	20.05
	$Z_L$	20
	$e_w$	22.5
	$e_L$	20
Thickness (mm)	$H_1$	6.4
Number of cells	$N_w$	6
	$N_L$	14
Maximum storage No. IC/Tray		84
Maximum storage No. IC/Inner box		420
Material		Carbon PP
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C MAX
Packing form		Dry pack