


# JEDEC TRAY

Tray Code	RENESAS Code	Previous Code
PTA61C	PLBG0256KA-A	BP-256C / BP-256CV
	PLBG0393KA-A	—

Unit:mm



The pin1 is located in the hatching portion

Position dimension of cells (mm)	$Z_w$	10.95
	$Z_L$	10.5
	$e_w$	14.25
	$e_L$	14
Thickness (mm)	$H_1$	7.62
Number of cells	$N_w$	9
	$N_L$	22
Maximum storage No. IC/Tray		198
Maximum storage No. IC/Inner box		1782
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack