

Supplemental Information

This Document Errata reflects changes required for the device datasheet of 83940DYI, 83940DYILF, 83940DKI and 83940DKILF.

Revision History

September 9, 2010: First version of documentation errata for this device.

Errata Item

Page 2, Table 2 Pin Characteristics – Erroneous device description in the datasheet for Output Impedance (R_{OUT}).

Only datasheet was corrected. There are no changes to the device.

FROM:

Symbol	Parameter	Test Conditions	Minimum	Typical	Maximum	Units
C_{IN}	Input Capacitance			4		pF
R_{PULLUP}	Input Pullup Resistor			51		k Ω
$R_{PULLDOWN}$	Input Pulldown Resistor			51		k Ω
C_{PD}	Power Dissipation Capacitance (per output)			6		pF
R_{OUT}	Output Impedance		7		28	Ω

TO:

Symbol	Parameter	Test Conditions	Minimum	Typical	Maximum	Units
C_{IN}	Input Capacitance			4		pF
R_{PULLUP}	Input Pullup Resistor			51		k Ω
$R_{PULLDOWN}$	Input Pulldown Resistor			51		k Ω
C_{PD}	Power Dissipation Capacitance (per output)			6		pF
R_{OUT}	Output Impedance		18		28	Ω