



Performance Comparison of IDT Tsi381 and Pericom PI7C9X110

80E2000_AN006_02

October 1, 2009

6024 Silver Creek Valley Road San Jose, California 95138

Telephone: (408) 284-8200 • FAX: (408) 284-3572

Printed in U.S.A.

©2009 Integrated Device Technology, Inc.

GENERAL DISCLAIMER

Integrated Device Technology, Inc. ("IDT") reserves the right to make changes to its products or specifications at any time, without notice, in order to improve design or performance. IDT does not assume responsibility for use of any circuitry described herein other than the circuitry embodied in an IDT product. Disclosure of the information herein does not convey a license or any other right, by implication or otherwise, in any patent, trademark, or other intellectual property right of IDT. IDT products may contain errata which can affect product performance to a minor or immaterial degree. Current characterized errata will be made available upon request. Items identified herein as "reserved" or "undefined" are reserved for future definition. IDT does not assume responsibility for conflicts or incompatibilities arising from the future definition of such items. IDT products have not been designed, tested, or manufactured for use in, and thus are not warranted for, applications where the failure, malfunction, or any inaccuracy in the application carries a risk of death, serious bodily injury, or damage to tangible property. Code examples provided herein by IDT are for illustrative purposes only and should not be relied upon for developing applications. Any use of such code examples shall be at the user's sole risk.

Copyright © 2009 Integrated Device Technology, Inc.
All Rights Reserved.

The IDT logo is registered to Integrated Device Technology, Inc. IDT is a trademark of Integrated Device Technology, Inc.

1. Performance Comparison of IDT Tsi381 and Pericom PI7C9X110

This report compares the IDT Tsi381 versus the Pericom PI7C9X110. It highlights the performance advantages of using the Tsi381 over the PI7C9X110.

This document discusses the following:

- “Throughput Measurements”
- “Simulation Measurements”
- “Lab Throughput Test Setup”

Terms

- Upstream transaction – In the context of a PCIe-to-PCI bridge, this transaction flow starts on a PCI bus and ends on a PCIe link.
- Downstream – In the context of a PCIe-to-PCI bridge, this transaction flow starts on a PCIe link and ends on a PCI bus.

Revision History

80E2000_AN006_02, Formal, October 2009

This document was rebranded as IDT. It does not include any technical change.

80E2000_AN006_01, Formal, December 2008

This is the first version of the document.

1.1 Throughput Measurements

This section consists of a lab analysis comparison between the Tsi381 and the PI7C9X110, as well as simulation throughput analysis of the Tsi381.

1.1.1 Lab Throughput Analysis

This section compares throughput measurements of the IDT Tsi381 and the Pericom PI7C9X110. Please note that the throughput tests do not include bidirectional traffic. Each test is of a single direction of a particular size and type of transaction.

Unless noted, the default register settings for the devices were used.

1.1.1.1 PCI Upstream Reads

This test used an Agilent E2960 PCIe Exerciser connected to a PCI target/Analyzer (E2928) through a bridge. The Agilent E2960 was used as a root complex. The bridge card connected to the Agilent PCIe exerciser backplane. A PCI exerciser/analyzer is connected to the bridge card, and is used to initiate read request cycles. The Tsi381 was tested with its default configuration state and with pre-fetching/Short Term Caching enabled.

This test provides a relative performance comparison between the bridges, and is not a maximum throughput comparison. This is due to limitations in the response time of the PCIe target, as well as delays in the PCI exerciser initiating back-to-back cycles.

For applications where performance is critical, it is important to enable short-term caching to maximize bus efficiency (this was enabled in the Tsi381).

Payload Size (Bytes)	PCI Bus Speed (MHz)	Tsi381 ^a Throughput (MBps)	Pericom PI7C9X110 Throughput (MBps)	IDT Performance Improvement
128	66	86.8	35.2	146%
64	66	59.3	20.4	189%
32	66	32.9	11.1	195%
16	66	17.4	5.6	206%
8	66	8.9	2.8	210%

a. The Tsi381's registers were configured as follows:

Prefetch Control Register (offset 0x0BC) = 0x03FFFFFFF.

PCI Miscellaneous Control and Status Register (offset 0x044) = 0x7D9F_1900 (this sets the Short Term Caching Enable bit).

Summary

The Tsi381 can obtain superior upstream read performance compared with the PI7C9X110 due to its short-term caching capability.

1.1.1.2 PCI Upstream Writes

This test used an Agilent E2960 PCIe Exerciser connected to a PCI-X Exerciser (E2929) through a 32-bit/66-MHz_64/133MHz PCI bridge card.

The hardware setup included an extra PCI-PCI bridge card that acted as a funnel for PCI data. The PCI exerciser used in the downstream test (Agilent E2928), however, cannot write data fast enough to saturate the bridge. In order to push as much data as possible through the bridge, a PCI-X exerciser running at 133 MHz was used to push data into the bridge faster than it can transfer it to the PCIe target. This resulted in retries on the PCI side of the bridge, and deemed it to be a good indication of the fastest upstream throughput.

Payload Size (Bytes)	PCI Bus Speed (MHz)	Tsi381 Throughput (MBps)	Pericom PI7C9X110 Throughput (MBps)	IDT Performance Improvement
128	66	212.3	214.9	-1.2%
64	66	189.5	189.3	0.1%
32	66	153.1	152.9	0.1%
16	66	86.6	86.8	0.2%
8	66	45.3	45.3	0%

Summary

The IDT Tsi381 and the Pericom PI7C9X110 have similar upstream write performance.

1.1.1.3 PCIe Downstream Reads

This test used an Agilent E2960 PCIe Exerciser connected to a PCI target/Analyzer (E2928) through a bridge. The Agilent E2960 was used as a root complex. The bridge card connects to the Agilent PCIe exerciser backplane. A PCI exerciser/analyzer is connected to the bridge card, and is used as a PCI target.

This test provides a relative performance comparison between the bridges, and is not a maximum throughput comparison. This is due to limitations in the response time of the PCI target, as well as delays in the PCIe exerciser initiating back-to-back cycles.

Payload Size (Bytes)	PCI Bus Speed (MHz)	Tsi381 Throughput (MBps)	Pericom PI7C9X110 Throughput (MBps)	IDT Performance Improvement
128	66	156.9	133.3	17.7%
64	66	93.9	83.3	12.7%
32	66	51.3	47.6	7.7%
16	66	27.7	25.6	7.8%
8	66	13.9	13.0	7.0%

Summary

The Tsi381 provides superior downstream performance compared with the Pericom PI7C9X110.

1.1.1.4 PCIe Downstream Posted Writes

This test used an Agilent E2960 PCIe Exerciser connected to a PCI target/Analyzer (E2928) through a bridge. The Agilent E2960 was used as a root complex. The bridge card connects to the Agilent PCIe exerciser backplane. A PCI exerciser/analyzer is connected to the bridge card., and is used as a PCI target.

Payload Size (Bytes)	PCI Bus Speed (MHz)	Tsi381 Throughput (MBps)	Pericom PI7C9X110 Throughput (MBps)	IDT Performance Improvement
128	66	162.8	143.1	13.7%
64	66	164.9	92.9	77.5%
32	66	76.2	54.2	40.5%
16	66	44.4	30.3	46.5%
8	66	24.2	15.2	59.2%

Summary

The Tsi381 has significantly better downstream write performance.

1.2 Simulation Measurements

1.2.1 Test Setup

The Tsi381's simulation throughput was measured in the upstream and downstream directions for both read and write transactions. The results for both measurements are explained in the following sections, and indicates the maximum sustained throughput data that can be attained for the Tsi381 under optimal circumstances.

The test results were derived from simulation. The Tsi381's simulation environment consists of the Tsi381 device with bus functional models (BFMs) on both the PCI and PCIe interfaces. The BFMs were used to initiate read and write transactions through the Tsi381, as well as provide an ideal target response. The PCI bus frequency was equal to 66 MHz for all tests. This provides a test environment that measures maximum throughput for various types of transactions.

1.2.2 Test Results

1.2.2.1 Upstream Writes

PCI Burst Size (bytes)	Maximum Sustained Throughput (MBps)
32	147.1
64	183.3
128	208.9

1.2.2.2 Upstream Reads

PCI Burst Size (bytes)	Maximum Sustained Throughput (MBps)
32	128.7
64	159.3
128	162.2

1.2.2.3 Downstream Writes

PCIe Data Payload Size (bytes)	Maximum Sustained Throughput (MBps)
32	144.8
64	179.9
128	197.7


1.2.2.4 Downstream Reads

PCIe Data Payload Size (bytes)	Maximum Sustained Throughput (MBps)
32	110.9
64	159.4
128	193.9

1.3 Lab Throughput Test Setup

This section describes the hardware test environment.


Figure 1: System Setup



- A Catalyst two-slot backplane with model number PX100 was used.
- The appropriate (Tsi381, PI7C9X110) evaluation board was connected directly into slot 1 of the Catalyst backplane.
- The Agilent E2928 PCI Exerciser/Analyzer card was plugged into the top slot of the evaluation board.
- An ATX power supply provided power to the PCI bus through a connector on the evaluation board.
- The Agilent PCIe Exerciser/Analyzer card was connected to slot 2 of the Catalyst backplane.
- The Catalyst backplane supplied power and reset to both boards, as well as clocking to the evaluation board.
- The Agilent PCIe Exerciser/Analyzer clock source was internal.
- The Agilent serial protocol mainframe was connected to the Agilent PCIe Exerciser/Analyzer card through the E2942A single probe Y-cable. This cable allowed the simultaneous use of one active probe board for the exerciser and analyzer (using two I/O modules).
- The Agilent Exerciser/Analyzer software operated on a Control PC. The PC was connected to the Agilent PCIe hardware through Ethernet.
- The Agilent PCI exerciser analyzer was connected to the Control PC through its proprietary fast-bus interface. The Control PC operated the Exerciser/Analyzer control software.
- The Control PC provided full control of stimulus and response of the PCIe and PCI sides of the bridge.

PCIe Performance Measurement Method

Throughput was monitored using the Agilent E2960 Protocol Tester Realtime Statistics display. This display measures card performance in megabytes per second (MBps).



CORPORATE HEADQUARTERS
6024 Silver Creek Valley Road
San Jose, CA 95138

for SALES:
800-345-7015 or 408-284-8200
fax: 408-284-2775
www.idt.com

for Tech Support:
email: ssdhelp@idt.com
phone: 408-284-8208
document: 80E2000_AN006_02