

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Mask ROM number	
-----------------	--

**RENESAS SINGLE-CHIP 16-BIT
MICROCOMPUTER M306H3MC-XXXXP
MASK ROM CONFIRMATION FORM**

Receipt	Date	
	Section head signature	Supervisor signature

(注) Note : Please fill in all items marked ※

※ Customer	Company name	TEL ()	Issuance signature	Submitted by	Supervisor
	Data issue	Date:			

※1. Confirmation

Name the product you order.
In order, one floppy disk is required per pattern.

Renesas processes the mask files generated by the mask file generation utilities out of those held on the floppy disks you give in to us, and forms them into masks. Hence, we assume liability provided that there is any discrepancy between the contents of these mask files and the ROM data to be burned into products we produce. Check thoroughly the contents of the mask files you give in.

Prepare 3.5 inches 2HD(IBM format) floppy disks, And store only one mask file in a floppy disk.

File code

--	--	--	--	--	--	--	--

 (hex)

Mask file name

--	--	--	--	--	--	--	--

 .MSK(alpha-numeric8-digit)

Note: When using the floppy disks, do not store the type No. to addresses 00000₁₆ to 0000F₁₆

※2. Mark specification

The mark specification differs according to the type of package. After entering the mark specification on the separate mark specification sheet(for each package), attach that sheet to this masking check sheet for submission to Renesas.

For the M306H3MC-XXXXP, submit the 116P6A mark specification sheet.

**RENESAS SINGLE-CHIP 16-BIT
MICROCOMPUTER M306H3MC-XXXFP
MASK ROM CONFIRMATION FORM**

※3. Usage Conditions

For our reference when testing our products, please reply to the following question about the usage of the products you ordered.

(1) Which kind of X_{IN}-X_{OUT} oscillation circuit used?

- Ceramic resonator Quartz-crystal oscillator
 External clock input Other()

What frequency do you use?

f(X_{IN}) = MHz

(2) Which kind of X_{CIN}-X_{COUT} oscillation circuit used?

- Ceramic resonator Quartz-crystal oscillator
 External clock input Other()

What frequency do you use?

f(X_{CIN}) = kHz

(3) Which operation mode do you use?

- Single-chip mode Memory expansion mode
 Microprocessor mode

(4) Do you use I²C(Inter IC) bus function?

- Not user Use

(5) Do you use IE(Inter Equipment) bus function?

- Not user Use

Thank you cooperation.

※4. Special item(Indicate none if there is no specified item)