



DCN	REV	DESCRIPTION	DATE	APPROVED
17899	03	REVISED DIM "b" MAX	6-26-90	NF



SYMBOLS	LIMITS	
	INCHES	
	MIN	MAX
A	.140	.165
A1	.015	.035
b	.015	.022
b1	.050	.070
C	.008	.012
D	.745	.760
E	.300	.325
E1	.247	.260
e	.090	.110
eA	.310	.370
L	.120	.150
ϕ	0°	15°
N	16	
Q1	.050	.070
S	.015	.035

JEDEC	EXCEPTIONS
STD-MS-001(AA)	NONE

TOLERANCES UNLESS OTHERWISE SPECIFIED
 FRAC DEC ANGLES
 ± - ± - ± -



Integrated Device Technology, Inc.
 3236 Scott Blvd., Santa Clara, CA 95051
 (408) 727-6116 TWX: 910-338-2070

APPROVALS	DATE
DRAWN <i>Ad</i>	7/88
CHECKED	
<i>NF</i>	6/90

16 LD P-DIP MKT DWG
 (300 MIL)

SCALE	SIZE	DRAWING NO.	REV
N/A	A	PSC-4014	03