




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
02	ADD "GREEN" BKG NOMENCLATURE	10/19/04	TU VU
03	COMBINE POD & LAND PATTERN	06/21/13	KS



Bell Pitch :	0.65	Substrate Thickness :	0.26
Bell Diameter :	0.40	Mold Thickness :	0.53


TOLERANCES		UNLESS SPECIFIED	
DECIMAL	ANGULAR	DECIMAL	ANGULAR
XX.X	XX.X	XX.X	XX.X
XX.XX	XX.X	XX.XX	XX.X
XX.XXX	XX.X	XX.XXX	XX.X

APPROVALS	DATE	TITLE
DRAWN <i>gyp</i>	02/17/04	BK/BKG 176 PACKAGE OUTLINE
CHECKED		6 x 15 mm BODY CTBGA
		0.65 mm PITCH
		DRAWING No.
		PSC-4128
		REV
		03

DO NOT SCALE DRAWING	SHEET 1 OF 2
----------------------	--------------


6024 SILVER CREEK
 VALLEY ROAD
 SAN JOSE CA, 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-8591
www.IDT.com


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
02	ADD "GREEN" BKG NOMENCLATURE	10/19/04	TU VU
03	COMBINE POD & LAND PATTERN	06/21/13	KS



RECOMMENDED LAND PATTERN DIMENSION

NOTE:

- 1) ALL dimensions are in mm, Angles in degrees.
- 2) Top down view, as view on PCB.
- 3) NSMD Land Pattern Assumed
- 4) Land Pattern Recommendation as per IPC-7351B generic requirement for surface mount design and Land Pattern.

TOLERANCES UNLESS SPECIFIED		APPROVALS	
DECIMAL	ANGULAR	DATE	
XX±		02/17/04	
XXX±			
XXXX			
 6024 SILVER CREEK VALLEY ROAD SAN JOSE CA, 95138 PHONE: (408) 284-8200 FAX: (408) 284-8591		TITLE BK/BKG 176 PACKAGE OUTLINE 6 x 15 mm BODY CTBGA 0.65 mm PITCH	
DRAWN	DATE	SIZE	DRAWING No.
09/04	02/17/04	C	PSC-4128
CHECKED			
DO NOT SCALE DRAWING			REV 03
			SHEET 2 OF 2