



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	01/08/11	DP
01	PACKAGE HEIGHT UPDATED	03/18/11	DP
02	PACKAGE HEIGHT UPDATED	04/29/11	JG




TOP VIEW

A	MAX.	SLP
	NDM.	1.15
	MIN.	1.10



BOTTOM VIEW



SIDE VIEW

TOLERANCES UNLESS SPECIFIED
 DECIMAL ANGULAR
 XXX± ±
 XXXXX±

APPROVALS DATE
 DRAWN DP 01/08/11
 CHECKED

SIZE C
 DRAWING No. PSC-4338
 DO NOT SCALE DRAWING

SHEET 1 OF 2

REV 02


6024 Silver Creek Valley Road
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-8591
 www.IDT.com

5.0x 3.2 mm BODY
 1.27 mm PITCH COL

ON/CNG10 PACKAGE OUTLINE


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	01/08/11	DP
01	PACKAGE HEIGHT UPDATED	03/18/11	DP
02	PACKAGE HEIGHT UPDATED	04/29/11	JG

PIN #1 IDENTIFICATION
CHAMFER 0.300 x 45°



CNG10 RECOMMENDED LAND PATTERN
(PCB TOP VIEW)

NOTES: ALL DIMENSIONS ARE IN MILLIMETERS.

TOLERANCES UNLESS SPECIFIED		 8024 Silver Creek Valley Road San Jose, CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-8591 www.idt.com	
DECIMAL	ANGULAR	TITLE	CN/CNG10 PACKAGE OUTLINE
XXX±	±	APPROVALS	DATE
XXXX±		DRAIN DP	01/08/11
XXXX±		CHECKED	
SIZE	DRAWING No.	REV	
C	PSC-4338	02	
DO NOT SCALE DRAWING		SHEET 2 OF 2	