


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	06/15/11	DP
01	UPDATE CHAMFER, b1, b2 DIMENSIONS	07/08/11	DP/KH
02	COMBINE POD and LAND PATTERN	4/1/13	RC
03	REMOVED A2 & A3	1/9/14	CM
04	ADD NOTE RECOMMENDED LAND PATTERN	2/25/14	JH



TOP VIEW

C-C SECTION VIEW

BOTTOM VIEW

TOLERANCES UNLESS SPECIFIED		6024 Silver Creek Valley Road	
DECIMAL	ANGULAR	San Jose CA 95138	
$\pm .1$	$\pm 1^\circ$	PHONE: (408) 284-8200	
XXX±		FAX: (408) 284-8591	
APPROVALS	DATE	TITLE	
DRAWN <i>JB</i>	04/25/11	CV/CV64 PACKAGE OUTLINE	
CHECKED		2.0 x 2.5 mm BODY	
		1.35 mm X Pitch, 1.62 mm Y PITCH	
SIZE	DRAWING No.	REV	
C	PSC-4355	04	
DO NOT SCALE DRAWING		SHEET 1 OF 3	


SYMBOL	MILLIMETER			INCH		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	----	----	0.90	----	----	0.035
A1	----	----	0.05	----	----	0.002
b1	0.67	0.72	0.77	0.026	0.028	0.030
b2	0.60	0.65	0.70	0.024	0.026	0.027
D	2.00 bsc			0.079 bsc		
E	2.50 bsc			0.098 bsc		
e1	1.62 bsc			0.064 bsc		
e2	1.35 bsc			0.053 bsc		
TOLERANCES OF FORM AND POSITION						
aaa	0.10			0.004		
bbb	0.10			0.004		
ccc	0.05			0.002		

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	06/15/11	DP
01	UPDATE CHAMFER, b1, b2 DIMENSIONS	07/08/11	DP/KH
02	COMBINE POD and LAND PATTERN	4/1/13	RC
03	REMOVED A2 & A3	1/9/14	CM
04	ADD NOTE RECOMMENDED LAND PATTERN	2/25/14	J.H

- NOTES :
1. ALL DIMENSIONS ARE IN MILLIMETERS.
 2. DIE THICKNESS ALLOWABLE IS 0.305 mm MAXIMUM.
 3. DIMENSIONING & TOLERANCES CONFORM TO ASME Y14.5M. -1994.
 4. THE PIN #1 IDENTIFIER MUST BE PLACED ON THE TOP SURFACE OF THE PACKAGE BY USING INDENTATION MARK OR OTHER FEATURE OF PACKAGE BODY.
 5. EXACT SHAPE AND SIZE OF THIS FEATURE IS OPTIONAL.
 6. PACKAGE WARPAGE MAX 0.08 mm.

TOLERANCES UNLESS SPECIFIED		6024 Silver Creek Valley Road	
DECIMAL	ANGULAR	San Jose CA 95138	
$\pm .1$	$\pm 1^\circ$	PHONE: (408) 284-8200	
XX±		FAX: (408) 284-8591	
XXX±			
APPROVALS	DATE	TITLE CV/CV64 PACKAGE OUTLINE	
DRAWN <i>gls</i>	04/25/11	2.0 x 2.5 mm BODY	
CHECKED		1.35 mm X PITCH, 1.62 mm Y PITCH	
		SIZE DRAWING No. PSC-4355	
		DO NOT SCALE DRAWING	
		SHEET 2 OF 3	

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	06/15/11	DP
01	UPDATE CHAMFER, b1, b2 DIMENSIONS	07/08/11	DP/KH
02	COMBINE POD and LAND PATTERN	4/1/13	RC
03	REMOVED A2 & A3	1/9/14	CM
04	ADD NOTE RECOMMENDED LAND PATTERN	2/25/14	J.H



RECOMMENDED LAND PATTERN DIMENSION

NOTES:

1. ALL DIMENSION ARE IN mm. ANGLES IN DEGREES.
2. TOP DOWN VIEW. AS VIEWED ON PCB.
3. COMPONENT OUTLINE SHOW FOR REFERENCE IN GREEN.
4. LAND PATTERN IN BLUE. NSMD PATTERN ASSUMED.
5. LAND PATTERN RECOMMENDATION PER IPC-7351B GENERIC REQUIREMENT FOR MOUNT DESIGN AND LAND PATTERN.

TOLERANCES UNLESS SPECIFIED		DECIMAL		ANGULAR	
XX±		E1°			
XXX±				 6024 Silver Creek Valley Road San Jose CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-8591	
APPROVALS	DATE	TITLE			
DRAWN <i>JB</i>	04/25/11	CV/CVG4 PACKAGE OUTLINE			
CHECKED		2.0 x 2.5 mm BODY 1.35 mm X Pitch, 1.62 mm Y PITCH			
		SIZE	DRAWING No.	REV	
		C	PSC-4355	04	
DO NOT SCALE DRAWING			SHEET 3 OF 3		


IDT™

6024 Silver Creek Valley Road
 San Jose CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-8591

www.IDT.com