





REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	1/14/13	RC
01	COMBINE POD & LAND PATTERN	7/15/13	KS




UNIT	A	A1	A2	A3	bp	c	D <sup>(1)</sup>	E <sup>(1)</sup>	e	H <sub>D</sub>	H <sub>E</sub>	L	L <sub>p</sub>	v	w	y	Z <sub>D</sub> <sup>(1)</sup>	Z <sub>E</sub> <sup>(1)</sup>	∅
mm	max	0.25	1.85	0.25	0.4	0.25	10.1	10.1	0.8	12.9	12.9	1.3	0.95	0.15	0.15	0.1	1.2	1.2	10°
		0.05	1.65		0.2	0.14	9.9	9.9		12.3	12.3		0.55				0.8	0.8	

NOTE:  
1. Plastic or metal protrusions of 0.25 mm per side are not included


TOLERANCES UNLESS SPECIFIED		 <b>IDT</b> 6024 Silver Creek Valley Road San Jose, CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-8591 WWW.IDT.COM
DECIMAL	ANGULAR	
XXX±	±	
XXXX±		
APPROVALS	DATE	TITLE
DRAWN	02/01/14/13	DIG44 PACKAGE OUTLINE
CHECKED		10mm SQ BODY 1.74 mm BODY 0.8 mm PITCH QFP
		SIZE
		C
		DRAWING No.
		PSC-4426
		REV
		01
DO NOT SCALE DRAWING		SHEET 1 OF 2

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	1/14/13	RC
01	COMBINE POD & LAND PATTERN	7/15/13	KS



RECOMMENDED LAND PATTERN DIMENSION

- NOTES:
1. ALL DIMENSION ARE IN mm. ANGLES IN DEGREES.
  2. TOP DOWN VIEW. AS VIEWED ON PCB.
  3. LAND PATTERN IN BLUE. NSMD PATTERN ASSUMED.
  4. LAND PATTERN RECOMMENDATION PER IPC-7351B LP CALCULATOR.

TOLERANCES UNLESS SPECIFIED		 <b>6024 Silver Creek Valley Road</b> San Jose, CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-8591 <a href="http://www.idt.com">www.idt.com</a>	
DECIMAL ±	ANGULAR ±	TITLE	DIG44 PACKAGE OUTLINE
APPROVALS	DATE	DRAWN	10mm SQ BODY
CHECKED		SIZE	1.74 mm BODY 0.8 mm PITCH QFP
		DRAWING No.	PSC-4426
		REV	01
DO NOT SCALE DRAWING		SHEET 2 OF 2	