




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	1/14/13	RC
01	COMBINE POD & LAND PATTERN	06/24/13	KS




DIMENSIONS (mm are the original dimensions)

UNIT	A	A1	A2	A3	b _p	c	D	D(1)	D _h	E(1)	E _h	e	HD	HE	L	L _p	v	w	y	Z _D (1)	Z _E (1)	theta
max.	1.2	0.15	1.05	0.25	0.27	0.20	14.1	7.1	7.1	14.1	7.1	0.5	16.15	16.15	1	0.75	0.2	0.08	0.08	1.15	1.15	7°
mm	1.2	0.05	0.95	0.17	0.09	0.09	13.9	6.1	6.1	13.9	6.1	0.5	15.85	15.85	1	0.45	0.08	0.08	0.85	0.85	0°	


Note
1. Plastic or metal protrusions of 0.25 mm maximum per side are not included.

TOLERANCES UNLESS SPECIFIED		DECIMAL ANGULAR	
XXX	±		
XXXX			
XXXXX			
APPROVALS	DATE	TITLE	
DRAWN	06/24/13	EVG100 PACKAGE OUTLINE	
CHECKED		14.0 mm SQ BODY	
		1.0 mm THICK 0.5 mm PITCH QFP	
SIZE	C	DRAWING No.	PSC-4422
DO NOT SCALE DRAWING		REV	01
		SHEET	1 OF 2




6024 Silver Creek Valley Road
San Jose, CA 95138
PHONE: (408) 284-8200
FAX: (408) 284-8591
www.IDT.com

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	1/14/13	RC
01	COMBINE POD & LAND PATTERN	06/24/13	KS



RECOMMENDED FOOT PRINT DIMENSION

- NOTES:**
1. ALL DIMENSION ARE IN mm. ANGLES IN DEGREES.
 2. TOP DOWN VIEW. AS VIEWED ON PCB.
 3. LAND PATTERN IN BLACK. NSMD PATTERN ASSUMED.
 4. LAND PATTERN RECOMMENDATION PER IPC-7351B LP CALCULATOR.

TOLERANCES UNLESS SPECIFIED		 IDT 6024 Silver Creek Valley Road San Jose, CA 95138 PHONE: (408) 284-8200 WWW.IDT.COM FAX: (408) 284-8591	
DECIMAL	ANGULAR	TITLE	ENG100 PACKAGE OUTLINE
XX±	±	DATE	14.0 mm SQ BODY
XXX±		APPROVALS	1.0 mm THICK 0.5 mm PITCH QFP
XXXX±		DRAWN	02/GC/14/13
		CHECKED	
		SIZE	C
		DRAWING No.	PSC-4422
		REV	01
DO NOT SCALE DRAWING		SHEET 2 OF 2	