






JEITA Package Code	RENASAS Code	Previous Code	MASS[Typ.]
P-HQFP160-28x28-0.65	PRQP0160JC-C	FP-160J	5.3g



Terminal cross section



Detail F

NOTE)
 1. DIMENSIONS*1*AND*2*
 DO NOT INCLUDE MOLD FLASH
 2. DIMENSION*3*DOES NOT
 INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	28	—
E	—	28	—
A ₂	—	3.20	—
H _D	31.7	32.0	32.3
H _E	31.7	32.0	32.3
A	—	—	3.56
A ₁	0.05	0.15	0.25
b _p	0.24	0.32	0.40
b ₁	—	0.30	—
c	0.12	0.17	0.22
c ₁	—	0.15	—
θ	0°	—	8°
[e]	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z _D	—	1.33	—
Z _E	—	1.33	—
L	0.6	0.8	1.0
L ₁	—	2.0	—