



JEITA Package code	RENESAS code	Previous code	MASS(TYP.)[g]
P-LFBGA353-15x15-0.65	PLBG0353JA-A	P353F1-65-FNF	0.61



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	14.90	15.00	15.10
E	14.90	15.00	15.10
w	—	—	0.20
e	—	0.65	—
A	1.31	1.41	1.51
A1	0.25	0.30	0.35
A2	—	1.11	—
b	0.35	0.40	0.45
x	—	—	0.08
y	—	—	0.10
y1	—	—	0.20
ZD	—	1.00	—
ZE	—	1.00	—