


## 68-PIN PLASTIC QFP (10x14)



detail of lead end

### NOTE

Each lead centerline is located within 0.15 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	16.8±0.4
B	14.0±0.2
C	10.0±0.2
D	12.8±0.4
F	0.8
G	0.8
H	0.30±0.10
I	0.15
J	0.65 (T.P.)
K	1.4±0.2
L	0.6±0.2
M	0.15 <sup>+0.10</sup> <sub>-0.05</sub>
N	0.10
P	2.2
Q	0.1±0.1
R	5°±5°
S	2.5 MAX.

S68GH-65-2AK-3