

JEITA Package Code

RENESAS Code

Previous Code




MASS[Typ.]

P-QFP80-14x14-0.65


PRQP0080JB-A

FP-80A/FP-80AV


1.2g



Terminal cross section



Detail F



NOTE)

1. DIMENSIONS*1*AND*2* DO NOT INCLUDE MOLD FLASH
2. DIMENSION*3*DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	14	—
E	—	14	—
A ₂	—	2.70	—
H _D	16.9	17.2	17.5
H _E	16.9	17.2	17.5
A	—	—	3.05
A ₁	0.00	0.10	0.25
b _p	0.24	0.32	0.40
b ₁	—	0.30	—
c	0.12	0.17	0.22
c ₁	—	0.15	—
θ	0°	—	8°
e	—	0.65	—
x	—	—	0.12
y	—	—	0.10
Z _D	—	0.83	—
Z _E	—	0.83	—
L	0.5	0.8	1.1
L ₁	—	1.6	—