




32-PIN PLASTIC SOP (13.34 mm (525))



detail of lead end



NOTE

Each lead centerline is located within 0.12 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	20.61 MAX.
B	0.78 MAX.
C	1.27 (T.P.)
D	$0.40^{+0.10}_{-0.05}$
E	0.15 ± 0.05
F	2.95 MAX.
G	2.7
H	14.1 ± 0.3
I	11.3
J	1.4 ± 0.2
K	$0.20^{+0.10}_{-0.05}$
L	0.8 ± 0.2
M	0.12
N	0.10
P	$3^{\circ+7^{\circ}}_{-3^{\circ}}$

P32GW-50-525A-1