


## 16-PIN PLASTIC ZIP (7.96 mm (325))



### NOTE

Each lead centerline is located within 0.25 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	21.59 MAX.
F	0.5±0.1
G	0.25
H	2.54
I	1.27
J	1.27 MAX.
K	1.0 MIN.
M	7.0 MAX.
N	2.8±0.2
Q	8.3 MAX.
V	0.25 <sup>+0.10</sup> <sub>-0.05</sub>
W	2.54
Y	3.3±0.7

P16V-254A-3