



JEITA Package Code	RENESAS Code	Previous Code	MASS (Typ) [g]
P-TSSOP8-0225-0.65	PTSP0008JD-B	s8gr-65-9jg-2	0.04

Unit: mm



NOTE
Each lead centerline is located within 0.10 mm of its true position (T.P.) at maximum material condition.

Reference Symbol	Dimensions in millimeters		
	Min	Nom	Max
D	2.90	3.00	3.10
D ₁	3.00	3.15	3.30
E	4.30	4.40	4.50
A ₂	0.95	1.00	1.05
A ₁	0.05	0.10	0.15
A	—	—	1.20
b _p	0.19	0.27	0.30
c	0.090	0.145	0.200
H _E	6.20	6.40	6.60
e	—	0.65	—
x	—	—	0.10
y	—	—	0.10
Z _D	—	—	0.80
L	—	0.50	—
L ₁	0.80	1.00	1.20
θ	0°	3°	8°