


TOP VIEW

SIDE VIEW



BOTTOM VIEW

NOTES:

1. JEDEC compatible.
2. All dimensions are in millimeters (mm) and angles are in degrees.
3. Tolerances of ± 0.05 mm apply to untoleranced dimensions.
3. Dimensions in parenthesis () are for reference only.

