




SIDE VIEW



TOP VIEW



SIDE VIEW



BOTTOM VIEW

**NOTES:**

1. All dimensions are in mm and angles are in degrees.
2. Use ±0.05 mm for the non-toleranced dimensions.
3. Numbers in ( ) are for references only.