












P9243-G/GB MP-A11 DEMO SCHEMATIC V1P0

5V: BPP 5W ONLY
QC/9V: BPP 5W, EPP 8W, APPLE 7.5W
QC/12V: BPP 5W, EPP 10W, SS AFC, APPLE 7.5W
16V-19V: BPP 5W, EPP 15W, SS AFC, APPLE 7.5W



NOTE 1 - FOD_ADJ (GPIO_A2) function is removed. Do not populate.
Use REA GUI to change defaults.

NOTE 2 - LED_PAT (GPIO_A3) function is removed. Do not populate.
Use REA GUI to change defaults.



THIS DOCUMENT CONTAINS INFORMATION PROPRIETARY
TO Renesas Electronics America, INC. (REA).
USE OR DISCLOSURE WITHOUT THE WRITTEN
PERMISSION OF AN OFFICER OF REA IS
EXPRESSLY FORBIDDEN

Title		
P9243-G/GB MP-A11 DEMO SCHEMATIC V1P0		
Size Custom	Document Number	Rev 1.0
Date: Thursday, May 28, 2020	Sheet 1	of 1