




CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PT521BM	PLQP0040JB-C	FP-40EV
	PLQP0040JB-D	FP-40CV
	PLQP0048KD-A	FP-48C / FP-48CV

Unit:mm



The pin1 is located in the hatching portion



Position dimension of cells (mm)	Z_W	15.4
	Z_L	15.4
	e_w	15
	e_L	15
	S_w	25
Thickness (mm)	H_1	7.6
	H_2	2.5
Number of cells	N_w	8
	N_L	20
Maximum storage No. IC/Tray		160
Maximum storage No. IC/Inner box		1600
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack/Non dry pack