




CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PT865B	PRQP0144KA-A	FP-144G / FP-144GV
	PRQP0144KB-A	FP-144J / FP-144JV

Unit:mm



The pin1 is located in the hatching portion



Position dimension of cells (mm)	Z_W	21.4
	Z_L	18.4
	e_w	31
	e_L	31
	S_w	25
Thickness (mm)	H_1	7.6
	H_2	2.5
Number of cells	N_w	4
	N_L	10
Maximum storage No. IC/Tray		40
Maximum storage No. IC/Inner box		400
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack