




# CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PT825B	PRQP0160JC-A	FP-160H / FP-160HV
	PRQP0160JC-C	FP-160J

Unit:mm



The pin1 is located in the hatching portion



Position dimension of cells (mm)	$Z_W$	27.1
	$Z_L$	25.25
	$e_w$	40.8
	$e_L$	37.9
	$S_w$	55
Thickness (mm)	$H_1$	8.7
	$H_2$	3
Number of cells	$N_W$	3
	$N_L$	8
Maximum storage No. IC/Tray		24
Maximum storage No. IC/Inner box		240
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack