

Vout	Iout Range	IDT Controller Part Number	Recommended Inductor	IDT DrMOS Options Part Number
0.85V	15A – 40A	ZSPM1501ZA1W0	330nH Würth Inductor P/N 744301033	ZSPM9000AI1R ZSPM9010ZA1R ZSPM9015ZA1R ZSPM9060ZA1R
1.00V	15A – 40A	ZSPM1502ZA1W0	330nH Würth Inductor P/N 744301033	
1.20V	15A – 40A	ZSPM1503ZA1W0	330nH Würth Inductor P/N 744301033	
1.50V	15A – 40A	ZSPM1504ZA1W0	470nH Würth Inductor P/N 744301047	
1.80V	15A – 35A	ZSPM1505ZA1W0	470nH Würth Inductor P/N 744301047	
2.00V	15A – 25A	ZSPM1506ZA1W0	470nH Würth Inductor P/N 744301047	
2.50V	Up to 20A	ZSPM1507ZA1W0	1000nH Würth Inductor P/N 7443310100	
3.30V	Up to 15A	ZSPM1508ZA1W0	2200nH Würth Inductor P/N 7443310220	
5.00V	Up to 10A	ZSPM1509ZA1W0	2200nH Würth Inductor P/N 7443310220	
0.85V	Up to 15A	ZSPM1511ZA1W0	680nH Würth Inductor P/N 7443310068	
1.00V	Up to 15A	ZSPM1512ZA1W0	680nH Würth Inductor P/N 7443310068	
1.20V	Up to 15A	ZSPM1513ZA1W0	680nH Würth Inductor P/N 7443310068	

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.