

No	Reference	Description	Specification	Parts Number	Manufacturer	Qty	Note
1	U1	MCU	RX671,100-pin LQFP,2-MB ROM	R5F5671EHDFP	Renesas	1	
2	X1	Crystal oscillator	8MHz,SMD,±100ppm	CX5032GA08000D0PRT03	KYOCERA	0	Unmounted
3	X2	Ceramic Resonators	8MHz,TH,±0.5%	CSTLS8M00G53-A0	Murata	0	Unmounted
4	X3	Crystal oscillator	32.768kHz,SMD,±20ppm	TFX-02S-32.768KHZ-J31936	RIVER ELETEC	0	Unmounted
5	C1,C2,C11,C20	Tantalum Capacitor	10uF,3528m,16V	TAJB 106 K 016	AVX	4	
6	C8,C14	Tantalum Capacitor	10uF,3528m,16V	TAJB 106 K 016	AVX	0	Unmounted
7	C3,C4,C7,C10,C13,C15,C21	Ceramic Capacitor	0.1uF,0603m,16V,±10%	GRM033C71C104K	Murata	7	
8	C5	Ceramic Capacitor	0.22uF,0603m,6.3V,±20%	GRM033C80J224M	Murata	1	
9	C6,C9,C12	Ceramic Capacitor	0.01uF,0603m,16V,±10%	GRM033B31C103K	Murata	3	
10	C16,C17,C18,C19	Ceramic Capacitor	1608m	GRM188	Murata	0	Unmounted
11	D1	Diode (Power)	Vr=50V,DO-214BA ,Io=1A	GF1A-E3(RoHS対応)	Vishay	1	
12	GND2,GND3	Test Pin (GND)	TH	LC-22-G (Black)	MAC-8	0	Unmounted
13	T1	Test Pin (Yellow)	TH	LC-22-G (Yellow)	MAC-8	0	Unmounted
14	CN2,CN3	25 pin x 2 row Connector	50極 2.54mm 2列 ストレート TH	FFC-50BMEP1	HTK	0	Unmounted
15	CN1	Angle type PMOD connector(SMD)	6-pin x 2, SMD	SMH-106-02-T-D	Samtec	1	
16	J3	3-pin Jumper(PTH)	3-pin TH	FFC-3AMEP1	HTK	0	Unmounted
17	J1,J2,J4,J5,J6	2-pin Jumper(PTH)	2-pin TH	FFC-2AMEP1	HTK	0	Unmounted
18	POWLED1,LED0,LED1	LED (Green)	Green,1608m,25mcd	SML-D12M8WT86	ROHM	3	
19	RES1,SW1	Tactile Switch	Tactile Switch, SMD	PTS645SM43SMTR92 LFS	C&K	2	
20	R3,R6,R7,R9,R12,R14,R16,R18, R19,R41,R42,R43,R45,R47	Resistor	0Ω,1608m,1/10W	MCR03EZPJ000	ROHM	14	
21	R4,R5,R8,R10,R11,R13,R17, R20,R23,R24,R40,R46,R48	Resistor	0Ω,1608m,1/10W	MCR03EZPJ000	ROHM	0	Unmounted
22	R1,R2,R21	Resistor	4.7kΩ,1005m,1/16W	MCR01MZPJ472	ROHM	3	
23	R27,R28,R44,R49,R50	Resistor	10kΩ,1005m,1/16W	MCR01MZPJ103	ROHM	5	
24	R15,R22,R30,R31	Resistor	1608m	MCR03 Series	ROHM	0	Unmounted
25	R25,R26,R29	Resistor	1kΩ,1005m,1/16W	MCR01MZPJ102	ROHM	3	
26	R32,R33,R34,R35,R36,R37,R38,R39	Resistor	200Ω,1005m,1/16W	MCR01MZPJ201	ROHM	8	
27	EU2	Low Dropout linear regulator	Fixed 1 Output 3.3V 300mA 8-DFN	ISL9005AIRNZ-T	Renesas	1	
28	ED1	Diode	Vr=20V,SOT-346,Io=1A	RB491D	ROHM	1	
29	EC4,EC5	Ceramic Capacitor	1uF,0603m,10V,±20%	GRM033R61A105M	Murata	1	
*							

REVISION HISTORY	Target Board for RX671 BOM List
------------------	---------------------------------

Rev	Date	Description	
		Page	Summary
1.00	Mar 1, 2021	-	First Edition issued