




TOP VIEW





SIDE VIEW



BOTTOM VIEW



SIDE VIEW


RECOMMENDED LAND PATTERN
(PCB Top View, SMD Design)

Reference Symbol	Dimension in mm		
	Min	Nom	Max
D	5.13	5.23	5.33
E	5.18	5.28	5.38
A2	1.70	1.80	1.90
HD	-	-	-
HE	7.80	7.90	8.00
D1	-	-	-
E1	-	-	-
A	-	-	2.15
A1	0.05	-	0.25
bp	0.41	-	0.50
c	0.20	-	0.25
θ	0.00	-	8.00
e	1.27 BSC		
y	-	-	0.08
LP	0.50	0.65	0.80
L1	-	1.31 REF.	-

NOTES:

- JEDEC compatible.
- All dimensions are in mm and angles are in degrees.
- Use ± 0.05 mm for the non-toleranced dimensions.
- Foot length is measured at gauge plane 0.25 mm above seating plane.