


# Icc vs Vcc (High-speed clock mode)

Prepared on Oct. 20, 2006

R5F21258SNFP(Topr=-20 to 85degrees C)  
R5F21258SDFP(Topr=-40 to 85degrees C)  
XIN = 20 MHz (square wave)  
divide-by-8  
High-speed on-chip oscillator off  
Low-speed on-chip oscillator on = 125 kHz

— 85degreesC  
— -40degreesC

— 25degreesC



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.