

Frequency vs Topr (High-speed on-chip oscillator mode)

Prepared on Oct. 20, 2006

R5F21258SNFP(Topr=-20 to 85degrees C)

R5F21258SDFP(Topr=-40 to 85degrees C)


High-speed on-chip oscillator on

VCC=5.5V, 3.3V

The FRA1 register is the value after reset.

— VCC=5.5V

— VCC=3.3V



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.