
UNIT: mm



MD300-2A

Length: 500 ± 2.0 Thickness: $0.5^{+0.2}_{-0.1}$ Tolerance: ±0.4

Material: Plastic (With Antistatic Finish)

| Applied Package | Quantity (pcs) |
|---------------------------|----------------|
| 8-pin Plastic DIP | 50 MAX. |
| 14-pin Plastic DIP | 25 MAX. |
| 16-pin Plastic DIP | 25 MAX. |
| 18-pin Plastic DIP | 20 MAX. |
| 20-pin Plastic DIP | 18 MAX. |
| 14-pin Plastic Shrink DIP | 30 MAX. |
| 16-pin Plastic Shrink DIP | 30 MAX. |
| 18-pin Plastic Shrink DIP | 25 MAX. |
| 20-pin Plastic Shrink DIP | 25 MAX. |
| 22-pin Plastic Shrink DIP | 20 MAX. |
| 24-pin Plastic Shrink DIP | 20 MAX. |