

I_{cc} vs V_{cc}

(High-speed clock mode)

Prepared on Sep. 10, 2007


R8C/26-27 Group

XIN = 10MHz

High-speed on-chip oscillator off

Low-speed on-chip oscillator on = 125kHz

- no-division -40 degrees C
- no-division 25 degrees C
- no-division 85 degrees C
- divided-by-8 -40 degrees C
- divided-by-8 25 degrees C
- divided-by-8 85 degrees C



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.