



TOP VIEW

BOTTOM VIEW




SIDE VIEW




DETAIL A

NOTES:


1. All dimensions are in millimeters (mm) and angles are in degrees
2. Tolerances of ±0.007mm apply to untoleranced dimensions
3. Dimensions in parenthesis () are for reference only



**RECOMMENDED LAND PATTERN
(Substrate Top View, NSMD Design)**



DETAIL B



**SIDE VIEW CROSS-SECTION OF
BUMP ON TRACE FROM DETAIL B**

NOTES:

1. All dimensions are in millimeters (mm) and angles are in degrees.
2. Land Pattern exhibits substrate pads for die bump connections.
3. A complete layout requires additional connections and ground patterns.