




<b>JEITA Package Code</b>	<b>RENESAS Code</b>	<b>Previous Code</b>	<b>MASS (Typ) [g]</b>
P-TSOP(2) 44-10.16×18.41-0.80	PTSB0044GG-A	—	0.46


Unit: mm



NOTE)

1. DIMENSIONS  $*1$  AND  $*2$  DO NOT INCLUDE MOLD FLASH.
2. DIMENSION  $*3$  DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimensions in millimeters		
	Min	Nom	Max
D	18.28	18.41	18.54
E	10.03	10.16	10.29
A <sub>2</sub>	—	0.985	—
A <sub>1</sub>	0.05	0.10	0.15
A	—	—	1.2
bp	0.3	—	0.45
c	0.1	—	0.21
$\theta$	0°	—	8°
H <sub>E</sub>	11.56	11.76	11.96
e	—	0.8	—
x	—	—	0.2
y	—	—	0.1
Z	—	0.805	—
L <sub>p</sub>	0.4	0.5	0.6
L <sub>1</sub>	—	0.8	—



Detail F