



Top View



Detail A




Side View

DIMENSIONS OF SUB-GROUP B1	
A max	1.95
bp min	0.35
bp max	0.49
e nom	1.27
HE min	5.80
HE max	6.30
Lp min	0.40
Z max	0.635

DIMENSIONS OF SUB-GROUP C1	
A min	1.55
A1 min	0.10
A1 max	0.30
A2 min	1.40
A2 max	1.80
c min	0.15
c max	0.25
D min*	4.80
D max*	5.00
E min*	3.80
E max*	4.00
k min	0.33
θ max	0°
θ max	8°

\* WITHOUT MOLD FLASH



RECOMMENDED LAND PATTERN  
(PCB Top View, SMD Design)

NOTES:

1. JEDEC compatible.
2. All dimensions are in mm and angles are in degrees.
3. Use  $\pm 0.05$  mm for the non-toleranced dimensions.
4. Foot length is measured at gauge plane 0.25 mm above seating plane.