

外形図 Outline drawing


Renesasコード PRBG0324GB-A

RDK-G-001281



1/1

ルネサスエレクトロニクス株式会社
Renesas Electronics Corporation

JEITA Package code	RENESAS code	MASS(TYP.)[g]
P-FBGA324-19x19-0.80	PRBG0324GB-A	1.10



Unit :mm



Reference Symbol	Dimension in Millimeters		
	Min.	Nom.	Max.
D	18.90	19.00	19.10
E	18.90	19.00	19.10
A	—	—	2.00
A ₁	0.30	0.35	0.40
e	—	0.80	—
b	0.49	0.54	0.59
x ₁	—	—	0.15
x ₂	—	—	0.08
y	—	—	0.10
y ₁	—	—	0.20
n	—	324	—
Z _D	—	1.10	—
Z _E	—	1.10	—

⊕	x ₁ (M)	S	A(M)	B(M)
	x ₂ (M)	S		