


Icc vs Vcc (High-speed clock mode)

Prepared on Oct. 20, 2006

R5F21258SNFP(Topr=-20 to 85degrees C)
R5F21258SDFP(Topr=-40 to 85degrees C)
XIN = 5 MHz (square wave)
no division
High-speed on-chip oscillator off
Low-speed on-chip oscillator on = 125 kHz

— 85degreesC — 25degreesC
— -40degreesC



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.