

# Frequency vs Vcc (High-speed on-chip oscillator mode)

Prepared on Oct. 20, 2006

R5F21258SNFP(Topr=-20 to 85degrees C)

R5F21258SDFP(Topr=-40 to 85degrees C)

Vcc=2.7-5.5V


High-speed on-chip oscillator on

The FRA1 register is the value after reset.

— 85degreesC

— 25degreesC

— -40degreesC



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.