

JEITA Package Code

RENESAS Code

Previous Code



MASS[Typ.]

P-HTFQFP64-10x10-0.50



PTQP0064KB-H

TFP-64TE/TFP-64TEV


0.25g



- NOTE)
 1. DIMENSIONS**1*AND*2*
 DO NOT INCLUDE MOLD FLASH
 2. DIMENSION*3*DOES NOT
 INCLUDE TRIM OFFSET.



Terminal cross section



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	10.0	—
E	—	10.0	—
A ₂	—	1.00	—
H _D	11.8	12.0	12.2
H _E	11.8	12.0	12.2
A	—	—	1.20
A ₁	0.01	0.07	0.10
b _p	0.16	0.21	0.26
b ₁	—	0.19	—
c	0.095	0.145	0.195
c ₁	—	0.125	—
θ	0°	—	8°
\bar{e}	—	0.5	—
x	—	—	0.08
y	—	—	0.10
Z _D	—	1.25	—
Z _E	—	1.25	—
L	0.4	0.5	0.6
L ₁	—	1.0	—