

I_{CC} VS f(XIN) (High-speed clock mode)

Prepared on Oct. 20, 2006

R5F21258SNFP(Topr=-20 to 85degrees C)

R5F21258SDFP(Topr=-40 to 85degrees C)

V_{CC}=5V


To_{pr}=85degrees C

High-speed on-chip oscillator off

Low-speed on-chip oscillator on = 125 kHz

— no division

— divide by 8



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.