


A0	±0.1	B0	±0.1	K0	±0.1	Ki	±0.1	E	±0.10	F	±0.1	P0	±0.1	P1	±0.1	P2	±0.1	D0	+0.1	D1	+0.1	T	±0.05	W	+0.2 -0.1
15.3		15.3		2.5		1.9		1.75		11.5		4.0		20.0		2.0		Ø1.5		Ø1.5		0.30		24.0	



TOLERANCES UNLESS OTHERWISE SPECIFIED
 DECIMAL 25
 X ± .25
 .XX ± .13
 .XXX ± .13
 APPROVALS _____ DATE _____
www.IDT.com



6024 Silver Creek Valley Road,
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-3572

TITLE:
 BB/BBG 160, BF/BFG 208/289 &
 BG/BGG 121 CARRIER TAPE

STOCK NO.	N/A	DRAWING NO.	MSC-3400-A	REV	00
DO NOT SCALE DRAWING			SHEET	1	OF 1