



$A_0 \pm 0.1$	$A_1 \pm 0.1$	$B_0 \pm 0.1$	$B_1 \pm 0.1$	$K_0 \pm 0.1$	$K_i \pm 0.1$	$E \pm 0.10$	$F \pm 0.1$	$P_0 \pm 0.1$	$P_1 \pm 0.1$	$P_2 \pm 0.1$	$D_0 + 0.1$	$D_1 + 0.1$	$T \pm 0.05$	$S_0 \pm 0.1$	$W \pm 0.3$
29.3	29.8	29.3	29.8	3.8	2.9	1.75	20.2	4.0	36.0	2.0	$\phi 1.5$	$\phi 2.0$	0.30	40.4	44.0

TOLERANCES UNLESS OTHERWISE SPECIFIED
 DECIMAL 25
 X ± .25
 .XXX ± .13
 APPROVALS _____ DATE _____
IDT
 www.IDT.com
 6024 Silver Creek Valley Road,
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-3572

DRAWN	DATE	TITLE: AL/ALG 784, BL/BLG/BR 784 & HM/HMG/HMH/RM 784 CARRIER TAPE	SCALE N/A
		STOCK NO. N/A	REV 00
		DRAWING NO. MSC-5715-A	SIZE 00
DO NOT SCALE DRAWING			SHEET 1 OF 1