



A0 ±0.1	B0 ±0.1	K0 ±0.1	K1 ±0.1	E ±0.10	F ±0.1	P0 ±0.1	P1 ±0.1	P2 ±0.1	Do +0.1	D1 +0.1	T ±0.05	So ±0.1	W ±0.2
23.3	23.3	2.6	1.8	1.75	20.2	4.0	32.0	2.0	∅1.5	∅2.0	0.30	40.4	44.0

TOLERANCES UNLESS OTHERWISE SPECIFIED
 DECIMAL 25
 X ± .25
 .XX ± .13
 .XXX ± .13

ANGLE ±.5°

APPROVALS DATE

WWW.IDT.COM

6024 Silver Creek Valley Road,
 San Jose, CA 95138
 PHONE: (408) 284-8200
 FAX: (408) 284-3572



TITLE: BB/BBG 376 & BC/BCG 484 CARRIER TAPE

STOCK NO. N/A

DRAWING NO. MSC-4706-A

REV 00

SCALE N/A

DO NOT SCALE DRAWING SHEET 1 OF 1